

Equipped with LED light, suitable for observation in dark places

**USB Type-C rechargeable**  
※ Charging cable included

**NLSL-10-1**  
Magnification **10x**

**NLSL-15-1**  
Magnification **15x**



Order No.	011296	011297
Model No.	NLSL-10-1	NLSL-15-1
Magnification	10x	15x
Field of View	26mm	14mm
Effective Diameter	28mm	28mm
Lens Material	Glass	
Reticle	φ 35×D1.3mm	
Body Size	φ 47×H59mm	
Weight	Approx. 110g	Approx. 112g
Operating Temperature	5°C~40°C	
Built-in Rechargeable Battery	Lithium-ion Battery	
Continuous Lighting Time	Approx. 40min.*	
Charging Time	Approx. 2hrs.	

\*The shortest time when the battery is fully charged. It may vary depending on usage condition.

**Point** Effective Dia **1.4 times\*** larger

※Compared to our previous model

Its effective diameter is 28mm, 1.4x larger than the previous model (LSL-35). A larger lens for easier visibility.

LSL-35 <Previous model> 20mm

NLSL-10-1 28mm

**1.4 times larger**

**Point** **4 times\*** brighter

※Compared to our previous model

In addition to the brightness, attenuation over time has been improved, making it brighter and easier to see.

**6 built-in LED Lights**  
For observation without worrying about the light source

**Rechargeable**  
Charging time : Approx. 2 hrs.

**Built-in rechargeable battery**  
Lithium-ion battery

**Point** **Scale plate and glass plate included**

Graduation scale with 0.1mm intervals. Can be replaced depending on the purpose.

**Accessories:**

- Reticle (pre-attached) x1
- 35mm glass plate (with case) x1
- Eyepiece cap x1
- Storage case x1
- USB charging cable (cord length: approx. 50cm) x1
- Cleaning cloth x1

■ Scale plate ■ Glass plate

**Point** **Two types available, selectable by magnification**

NLSL-10-1 (10x)

NLSL-15-1 (15x)

### LOUPE NL-5 / NL-10 / NL-15 / NL-22

■ A basic magnifying glass with excellent cost performance.



Order No.	NEW! 011287	NEW! 011288	NEW! 011289	NEW! 011290
Model No.	NL-5	NL-10	NL-15	NL-22
Magnification	5x	10x	15x	22x
Field of View	34mm	22mm	12mm	3.5mm
Effective Diameter	25mm	24mm	18.5mm	12mm
Lens Material	Glass			
Body Size	φ38×H67mm	φ34×H42mm	φ36×H33mm	φ36×H24mm
Weight	Approx. 25g	Approx. 25g	Approx. 18g	Approx. 12g


Accessories: ● Cleaning cloth x1

### SCALE LOUPE NSL-10-S / NSL-10-1

■ 10x magnification scale loupe with a wide field of view and easy to use.



NSL-10-S



Accessories: ● Reticle (pre-attached) x1 ● Storage case x1  
● Eyepiece cap x1 ● Cleaning cloth x1


Order No.	011291	011292
Model No.	NSL-10-S	NSL-10-1
Magnification	10x	
Field of View	26mm	
Effective Diameter	20mm	
Lens Material	Glass	
Reticle	φ35×D1.3mm	
Body Size	φ45×H45mm	
Weight	Approx. 73g	

### SCALE LOUPE NSL-15-1 / NSL-20-S / NSL-30-S

■ Scale loupe with higher magnifications of 15x, 20x, and 30x for detailed observation.



NSL-15-1



Accessories: ● Reticle (pre-attached) x1 ● Storage pouch x1  
● Cleaning cloth x1


Order No.	011293	011294	011295
Model No.	NSL-15-1	NSL-20-S	NSL-30-S
Magnification	15x	20x	30x
Field of View	12mm	10mm	5mm
Effective Diameter	16mm		
Lens Material	Glass		
Reticle	φ26×D1.6mm		
Body Size	φ35×H38mm	φ35×H34mm	φ35×H31mm
Weight	Approx. 35g		

### CLIP LOUPE NPL-50 / NPL-25

■ High-magnification loupe with a clip, convenient to carry around.



NPL-50



**How to use**  
While looking through the eyepiece, adjust the focus by tilting the acrylic part forward and backward, using the tip as a pivot point.

**Note** Observation Target  
Due to the design, the image seen through the loupe will be upside down.

Order No.	011298	011299
Model No.	NPL-50	NPL-25
Magnification	50x	25x
Field of View	2mm	3mm
Effective Diameter	6.8mm	
Lens Material	Glass	
Body Size	φ13×L125mm(Without the clip)	
Weight	Approx. 22g	

※Weight, size, and other details are approximate.  
※The appearance and specifications are subject to change without prior notice due to product improvements.  
※The color may slightly differ between the printed materials and the actual product.

**Niigata Seiki Co., Ltd.**

5-3-14, Tsukanome, Sanjo, Niigata, Japan, 955-0055  
Tel.: +81-256-33-5522 Fax.: +81-256-33-5518  
MAIL intl.sales@niigataseiki.co.jp  
URL https://www.niigataseiki.net/en/

### Distributors